

Mobile x-ray

- * Single focus
- * Full wave rectifier combined x-ray generator

Control

- * 90 KVP - 100 mA
- * Normal frequency 220 V — 50 HZ
- * Contains:
 - * KV : From 40 to 90 kVP. step 1 kVP
 - * mA : from 25 to 100 mA (25-50-75-100)
 - * Time : From 0.01 to 3 seconds

X-Ray Tube

- * x-ray tube focus 4.3 mm

Collimator

- * Collimator max. film size at 65 cm focal distance : 35 *35 cm
- * Halogen lamp : 24 v – 75 w



F-100