

Mobile x-ray

- * Single focus
- * Full wave rectifier combined x-ray generator

Control

- * 90 KVP - 50 mA
- * Normal frequency 220 V — 50 HZ
- * Contains:
 - * KV : From 40 to 90 kVP. step 1 kVP
 - * mA : from 15 to 50 mA (15-40-50)
 - * Time : From 0.01 to 2.5 seconds

X-Ray Tube

- * x-ray tube focus 2.6 mm

Collimator

- * Collimator max. film size at 100 cm focal distance : 40*40 cm
- * Halogen lamp : 24 v – 75 w



F-50